

TKH-MOUSE-SCROLL-IP68-BLACK-LASER
INDUMOUSE



TKH-MOUSE-SCROLL-IP68-GREY-LASER
INDUMOUSE



PRODUCT FEATURES

- Medical grade mouse with plastic bottom plate and laser sensor
- Ergonomic shape with two mousebuttons and three-button scroll function
- Due to the symmetric shape it's suitable for right-hand and also left-hand operation
- Comfortable touch and operation
- Completely water and dust proof
- Easy to clean and to disinfect
- Germs and pathogens are prevented from growing due to antimicrobial properties
- Resolution adjustable in four levels from 400 to 1600 cpi

SPECIFICATION


Number keys:	5	Protection level:	IP68
Housing material:	silicone	Interface:	USB
Bottom panel material:	plastic	USB compatibility:	compatible with USB 2.0
Colour:	grey, black	Cable length:	approx. 2 m
Keyswitch technology:	short travel keys	Operating temperature:	-25 °C to +70 °C
Switching cycles:	appr. 3 mill. (per key)	Storage temperature:	-25 °C to +80 °C
Operating principle:	laser	Dimensions:	116 x 62 x 38.6 mm
Resolution:	400, 800, 1200 oder 1600 cpi (adjustable)	Weight:	160 g
Scrollfunction:	3 scrollbuttons	Certifications:	CE, RohS, REACH, EMC
		Warranty:	4 years on the electrical function

Art.No.	Product description	Colour
KH18218	TKH-MOUSE-SCROLL-IP68-GREY-LASER-USB	Grey
KH19216	TKH-MOUSE-SCROLL-IP68-BLACK-LASER-USB	Black


Other configurations and interfaces on request.

Subject to modifications and errors

TECHNICAL DRAWING



Mouse functions when using standard Windows® drivers



Resolution adjustment:

Resolution is adjustable in 4 levels: 400, 800, 1200 and 1600 cpi. Keep left and right mousebutton pressed at once and adjust the resolution with the scrollbuttons:

- * Scroll-up button: higher resolution
- * Scroll-down button: lower resolution

Subject to modifications and errors