

# PACF212CO W

12NC: 859991643650

GTIN (EAN) code: 8003437629877

Whirlpool

SENSING THE DIFFERENCE



- Type: Portables
- BTU cooling capacity: 12000
- Energy class cooling: A
- Main colour of product: White
- 6th Sense
- Sleep mode
- Jet function
- Around U function
- Dehumidification function
- Filter type: Washable
- Temperature display (°C): Yes
- Remote control: Yes
- Cooling sound power value for Indoor unit: 61
- EER Cooling: 2.6
- Refrigerant gas type: R290
- Container Loading Capacity (20'/40'/40'HQ): 130/264/394
- Gross weight (kg): 35.8
- Net weight (kg): 31.6
- Dimensions Indoor unit HxWxD: 718x442x373 mm
- Depth packed Indoor unit: 420
- Gross weight Indoor unit: 36
- Net weight Indoor unit: 32

## Whirlpool air conditioner - PACF212CO W

This Whirlpool freestanding air-conditioner features: energy efficiency class A. White color. Portable air conditioner, to easily move your air conditioner wherever you need. On/Off cool. 6th SENSE, the temperature sensor automatically evaluates the temperature of the room and makes the ideal combination of the operational functions in order to get the best comfort ever.



### Autoclean Function

Your Air Conditioner is preventing the growth of harmful micro-organisms, thanks to AutoClean function drying out the moisture inside the product keeping it dry and clean.



### Jet Cooling Function

Thanks to Jet Cooling Function this product is the perfect ally to restore the ideal temperature in your room, quickly. - 5°C in just 10 minutes\* as you don't have to wait to fully enjoy your well-being at home. \* Jet cooling: Referred to PACF212CO W portable model with Jet function. Test condition settings: indoor temperature 30°C, room size 13.9m2.



### Sleep mode - Portable

Thanks to Sleep Mode the led panel will turn off at night to avoid any disturbance as you can enjoy a comfortable sleep.



### 12000 BTU

12000 BTU cooling capacity, recommended for rooms of 14.5 - 20 m2.



### Compact Design

Modern design, very easy to move from one room to the other thanks to the wheels.



### Dehumidification function

You can now easily and quickly manage the humidity level, feeling more comfortable when it is very hot or cold, thanks to the Dehumidification function, removing more than 2L of water from the room in 1 hour\*. \*Referred to PACF212CO W portable model with dry function. Test condition settings: indoor temperature 30°C with 80% humidity, room size 13.3m2.



### New Silent mode

SUPER QUIET WITH SILENT MODE. UP TO -70%\*. Thanks to an unique operating mode in which evaporator and condenser work both at low fan speed, the product is running very quietly \*Based on a 5 DbA reduction in sound power comparing normal operating mode with maximum evaporator and condenser speed and silent mode with low evaporator and condenser speed. Measures conducted in internal laboratories, according to EN 12102.

# PACF212CO W

12NC: 859991643650

GTIN (EAN) code: 8003437629877

**Whirlpool**

SENSING THE DIFFERENCE

## DIMENSIONS

Current (A)	6
Frequency (Hz)	50
Depth IDU	373
Depth packed IDU	420
Gross weight IDU	36
Height IDU	718
Height packed IDU	885
Net weight IDU	32
Width IDU	442
Width packed IDU	495

## TECHNICAL FEATURES

Auto defrost	No
Dehumidification function	Yes
Room temperature display	Yes
Refrigerant gas type	R290

## PERFORMANCES

Energy class cooling	A
Energy class heating	N/A
Annual energy consumption during cooling season - kWh/annum	0
Annual energy consumption during heating season average (Green) - kWh/annum	0
Capacity Range Cooling Max	0
Capacity Range Cooling Min	0
Capacity Range Heating Max	0
Capacity Range Heating Min	0
Cooling sound power value for IDU	61
COP Heating	0
Declared capacity (kW)	0
EER Cooling	2.6
Heating sound power value for IDU	0
Rated capacity heating (kW)	0
Sound pressure noise level IDU - Silent mode	0
Working T° Range Cooling - Indoor range	21°C - 35°C
Working T° Range Cooling - Outdoor range	N/A
Working T° Range Heating - Indoor range	N/A
Working T° Range Heating - Outdoor range	N/A
Max current Cooling	7
Max current Heating	0