

Slotted rod holder, shape E2

For turning tools with cylindrical shanks

ORION[®]

Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm²
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground
- Internal and external coolant supply
- Vibration damping



Art. no.	22778 187
Brand	ORION
Manufacturer Part Number	22778187
VDI mount diameter	30 mm
Clamping diameter	16 mm
Length	22 mm
Projecting length	88 mm
Gross Weight	1.800 kg
Product Group	2AC

EAN

4053625465712