

Clamping tool assortments

Basic assortment



Application:

For conventional clamping on machine tables with T-grooves, ideal for toolmaking.

Execution:

- All parts made of heat-treated steel
- Rolled thread
- T-slot screws heat-treated

Delivery:

Ref. no. 26152140: Clamp, 2 pcs. 14×100 mm, 2 pcs. 14×160 mm, clamping supports 4 pcs. Size 2, 4 pcs. Size 3, T-slot screws, 2 pcs. M14×16×63 mm; 4 pcs. M14×16×100 mm; 4 pcs. M14×16×160 mm stud bolts 2 pcs. Size M14×100, 2 pcs. Size M14×160, high nuts 6 pcs. Size M14, extension nuts 2 pcs. Size M14, washers 6 pcs. Size M14,



Art. no.	26152 140
Brand	AMF
Manufacturer Part Number	83899
Suitable for groove width	14 mm
Suitable for thread	M12
Tension force	20 kN
Clamping height	165 mm
Weight	10 kg
Gross Weight	9.600 kg
Product Group	260

EAN

4020772083892