

Electronic outside micrometer

with disc-shaped measuring faces

Mitutoyo

Application:

For measuring tooth span on cogs, for recesses, groove distances etc.

Execution:

- measuring faces made of hardened steel
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)
- IP65
- Digimatic

Advantage:

- Accesses hard-to-reach measuring points

Delivery:

Includes box, adjustment wrench, standard setting (25 mm or more), adjustment wrench, battery



Art. no.	32017 582
Brand	MITUTOYO
Manufacturer Part Number	323-353-30
Display	Digital
Min./max. length measuring range in inches	3-4 in
Digit increment	0.00005 in
Measuring surface diameter	20 mm
IP protection class	IP 65
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Origin (Dimension preset), Hold-function (AE lock), Automatic switch-off
Min./max. measurement force	5-10 N
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Bracket depth	60 mm
Measuring spindle increments	0.5 mm
Calibration Group	D
Gross Weight	1.280 kg
Product Group	3MA

EAN

4946368689609