

Balancer with load capacity of 0.4-6.5 kg

Type 7228, cable extraction 1600 mm

AUTOSTAT

Application:

Can be used with the following tools and devices, e.g. compressed air devices, electric devices, paint spray guns, cable-binding pliers, nailing devices, flue gas swivelling arms, robot power supply line, welding pliers, packaging devices etc.

Execution:

- Housing made of extremely shock-resistant special plastic
- Suspended with rotating screw snap hooks
- Infinitely adjustable load, via notches
- The load is attached via a safe screw snap hook
- Cable feed limitation is impact absorbing and adjustable
- Rope is infinitely variable in its length via a rope clamp
- If required, the cable can be replaced very easily
- Safety device: Fall arrester in line with DIN 15112 included in scope of delivery, spring safety device, riveted special motive spring, cable drum, can be blocked, push clamp for securing the cable end
- Working area: Cable extraction: 1600 mm, ropes in special lengths available on request

Advantage:

- Effortless work



Art. no.	77000 586
Brand	AUTOSTAT
Manufacturer Part Number	77000586
Min. load-carrying capacity	0.4 kg
Max. load-carrying capacity	1.2 kg
Type	7228
With automatic locking	No
Max. cable pull-out length	1600 mm
Adjustable cord length	Yes
Wire cable diameter	3 mm
Replaceable cord	Yes
Cord in-feed restriction	Absorbs impacts, adjustable
Material of cable drum	Highly abrasion-proof plastic
Suspension type	Freely rotating and pivot screw karabiner hook
Load attachment	Screw Karabiner hook
Material of housing	Plastic
Housing width	141 mm
Housing thickness	71 mm
Colour of housing	Orange
Height	460 mm
Spring design	Riveted special mainspring
With overrotation protection	No
Spring breakage protection	No
Number of springs	1 PCS
DIN	15112
Gross Weight	1.422 kg
Product Group	772

EAN

4039247366521