

**GH506 / GH506B / GH466 /  
GH466B / FC325 / GH213  
GH810 (-12 to -32)**

Nipples with  
wire trap


Nippel mit  
Ausreiß-  
sicherung

Nipples avec  
gorge pour  
retenir les  
nappes

Nipples con  
protezione da  
strappo

Manguito  
roscados para  
seguro de  
arranque

GH506(B)/FC325/GH466(B)/GH213/GH810




**DSB**

**DKO Female Swivel, Heavy Duty, 90° Elbow**  
**Dichtkopf DKOS, schwere Baureihe, 90° Krümmer**  
**DKO série S, coude 90°**  
**Femmina girevole DKOS a 90°, serie pesante**  
**Hembra loca DKOS acodado a 90°, serie pesada**

Part Number GH506(B)/FC325/ GH810-12,-16	Part Number GH466(B)/GH213-24,-32 GH810-20,-24,-32	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E mm	K Ø mm	HEX [1]	HEX [2]
1W16DSB12		M30x2,0		20	19	-12	110,4	58,4	54,0	15,1			
1W16DSB12.120		M30x2,0		20	19	-12	110,4	58,4	120,0	15,1			
1W20DSB12		M36x2,0		25	19	-12	124,8	72,8	65,0	15,1		46	
1W20DSB12.077		M36x2,0		25	19	-12	124,8	72,8	76,5	15,1		46	
1W20DSB12.100		M36x2,0		25	19	-12	130,9	78,9	101,5	15,1		60	
1W20DSB12.150		M36x2,0		25	19	-12	123,4	81,7	150,0	15,1		60	
1W20DSB16		M36x2,0		25	25	-16	144,2	77,6	74,0	19,6		41	
1W25DSB16		M42x2,0		30	25	-16	155,6	89,0	76,0	19,6		50	
1W25DSB16.085		M42x2		30	25	-16	148,6	81,9	84,5	19,6		50	
1W25DSB16.140		M42x2		30	25	-16	155,6	89,0	140,0	19,6		50	
1W25DSB20.083		M42x2		30	31	-20	153,5	78,1	82,5	25,5		50	
1W25DSB20.83V		M42x2		30	31	-20	153,5	78,1	82,5	25,5		50	
1W32DSB20	1W32DSB20	M52x2,0		38	31	-20	185,0	110,1	89,0	25,5		60	
1W32DSB24	1W32DSB24	M52x2,0		38	38	-24	195,0	96,5	93,5	30,0		60	

GH506(B)/FC325/GH466(B)/GH213/GH810



**EK**

**24° Male, Heavy Duty**  
**Außengewindeanschluss 24°, schwere Baureihe**  
**Mâle 24° série forte**  
**Maschio metrico 24°, serie pesante**  
**Macho fijo de 24°, serie pesada**

Part Number GH506(B)/FC325/ GH810-12,-16	Part Number GH466(B)/GH213-24,-32 GH810-20,-24,-32	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E mm	K Ø mm	HEX [1]	HEX [2]
1W16EK12		M30x2,0		20	19	-12	86,4	34,4		15,1		32	
1W20EK12		M36x2,0		25	19	-12	88,4	36,4		15,1		41	
1W25EK16		M42x2,0		30	25	-16	110,0	43,4		19,6		46	
1W32EK20	1W32EK20	M52x2,0		38	31	-20	124,4	49,5		25,5		55	