




ZDO6H050MSS0010E15

Connection technology



Product characteristics

Splitter box

Cable with M12 connector

Gold-plated contacts

Electrical data

Electrical design

Operating voltage [V]

AC/DC
30 AC/DC; "supply class 2" to cULus.

Max. total current load [A]

12

Max. current load per location [A]

4 *)

Environment

Ambient temperature [°C]

-25...40

Ambient temperature (moving) [°C]

-5...60

Protection

IP 67; (enclosure type 1)

Mechanical data

Design

6 way

Housing materials

PA

Tightening torque for knurled nut [Nm]

0.8...1.5

Weight [kg]

0.864

Electrical connection

Connection

PVC cable / 10 m; 5 x 0.5 mm²; Ø 6.3 mm



Sheath colour

black

Wiring

EBC043 - Splitter box - eclass: 27279219 / 27-27-92-19

Core colours
 BK black
 BN brown
 BU blue
 GN/YE green/yellow
 WH white



Accessories	
Accessories (included)	6 labels
Remarks	
Remarks	*) 2 A per pin; 8 A per group
Pack quantity [piece]	1
Other data	
Ports	M12