

PASSIVE-DI0° PLASTIC,6XM12,5POL,PRE-WIRED CABLE

5.0m PUR-JB 12*0,34+3*0,75

6-way, 5-pole

PUR/PVC


5.0 m

with LED for digital PNP-signals 24 V DC


Further cable lengths on request.

[Link to Product](#)**Illustration**

M12 Females 5-pole



stay connected



Product may differ from Image

Approvals



Technical Data

Operating voltage	24 V DC
Operating voltage indicator	LED (green)
Signal per port	2
LED display per port	LED (yellow) per signal (PNP)
Operating current per contact	max. 4 A
Total current	max. 8 A
Locking of ports	Screw thread M12 × 1 mm

Cables

No./diameter of wires	12×0.34 + 3×0.75 mm ²
C-track properties	2 Mio.
Material (jacket)	PUR/PVC
Outer diameter	approx. 9.8 mm
Bend radius (moving)	12 × outer Ø
Cable number	388

General data

Dimensions H × W × D	100.5×54.5×25 mm
Protection	IP67 inserted and tightened (EN 60529)
Temperature range	-20...+80 °C

Contact layout

Contact 1	(+)
Contact 2	(NC)/(S2)
Contact 3	(-)
Contact 4	(NO)/(S1)

Contact 5 (Earth)

Commercial data

country of origin	CZ
customs tariff number	85444290
minimum order quantity	1