



INSTA CONTACTOR WITH 4 NO CONTACTS
CONTACT FOR AC 230, 400V 25A ACTIVATION
ACDC24V

Figure similar

Model		
product brand name		SENTRON
Product designation		Insta contactors
Protection class		
Protection class IP		IP20
Dissipation		
Active power loss		
<ul style="list-style-type: none"> for rated value of the current / with AC / in hot operating state / per pole 	W	2.2
Main circuit		
Operating voltage / Rated value		
<ul style="list-style-type: none"> minimum 	V	400
<ul style="list-style-type: none"> maximum 	V	400
Operating current / Rated value	A	24
Control current		
Control supply voltage / Rated value	V	24
<ul style="list-style-type: none"> maximum 	V	24
Product details		
Product component / Slide for manual operation		No
Product expansion / can be installed / supplementary devices		Yes
Number		
Number of NC contacts		0

Number of NO contacts		4
-----------------------	--	---

Mechanical Design

Height	mm	90
Width	mm	35
Depth	mm	71
Installation depth	mm	64
Number of width units		2

Certificates

Equipment marking / acc. to DIN EN 61346-2		Q
--	--	---

General Product Approval	Declaration of Conformity
---------------------------------	----------------------------------



[other](#)



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5TT50302>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/5TT50302/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT50302

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015