

QUICK RELEASE SAFETY COUPLINGS WITH BUTTON- ISO C



Description


Pressing the button first decompress the line, then with a second press of the button where there is a safe release of the coupling without the risk of whiplash.

Standards: ISO 4414 - DIN EN 983 - ISO 6150 Series C

Composite materials containing a metal element.

Port size: 6 mm

Flow: 833l/min to 6 bars using Delta P 10%.



Applications


Compress air

Temperature limits: Operating temperature: -15/+70 °C

Parallel Female Quick Coupling




CODE	CONNECTION	A	B	C
736002	G1/4	54	28	23
736003	G3/8	62	28	23
736004	G1/2	62	28	23



Parallel Male Quick Coupling




CODE	CONNECTION	A	B	C
736006	G1/4	62	28	23
736007	G3/8	62	28	23
736008	G1/2	64	28	23



Hose Tail Quick Coupling




CODE	Hose Internal Diameter	A	B	C
736012	6	78	28	23
736013	8	78	28	23
736014	10	78	28	23



Parallel Female Plug




CODE	CONNECTION	A	B
736017	G1/4	50	17
736018	G3/8	54	24
860298	G1/2	53	28



Taper Male Plugs



CODE	CONNECTION	A	B
736020	G1/4	48	14
736021	G3/8	52	17
860299	G1/2	64	28



Hose Tail Plugs



CODE	Hose Internal Diameter	A
736023	6	62
736024	8	62
736025	10	62
736026	13	62

