

Mechanical characteristics

cables

interface dimensions acc. to assembly code
 centre conductor
 outer conductor
 mating life

Components

centre contact
 outer contact
 other metal parts
 crimp ferrule
 insulator
 gasket

Electrical characteristics

impedance
 return loss
 working voltage
 voltage proof
 insulation resistance
 contact resistance
 centre contact
 outer contact

Environmental

operating temp.
 RoHS compliant

Mechanische Eigenschaften

Kabel

Steckgesicht nach Montageanleitung
 Innenleiter
 Außenleiter
 Steckzyklen

Bauteile

Innenkontakt
 Außenkontakt
 sonstige Metallteile
 Crimprohr
 Isolierung
 Dichtung

Elektrische Eigenschaften

Wellenwiderstand
 Rückflussdämpfung
 Betriebsspannung
 Prüfspannung
 Isolationswiderstand
 Durchgangswiderstand
 Innenkontakt
 Außenkontakt

Umgebung

Betriebstemperatur
 RoHS konform

G27 (1,0/4,6-6,7):
 ① ② 1,0/4,8 AF Draka; 1,0/4,8 Bedca; 1694A Belden HDTV; 3093A Belden; 7710A Belden; 7711A Belden; 7712A Belden; 7713A Belden; 9248 Belden; Image 720 Argosy; SDV-F Canford; SDV-L Canford; VB1890 GEPCO; VK7/1,0 FRLS 1,0/4,6 Percon
 ③

IEC 61169-8
 A4207
 Crimp
 Crimp
 >500 ②

Materials / Material


CuZn39Pb3
 CuZn39Pb3
 GD-ZnAl4Cu1
 SF Cu w
 PE green/grün (similar/ähnl. RAL 6001)
 silicone / Silikon

Finish / Oberfläche

Cu1Ni2Au0,8
 Cu2Ni5
 Zn/Cu6Ni6
 Ni5

75 Ω
 typ.: 1 GHz - 36 dB; 2 GHz - 31 dB; 3 GHz - 29 dB
 ≤ 0,5 kV_{eff} / 50 Hz
 1,5 kV_{eff} / 50 Hz
 ≥ 5 GΩ
 ≤ 20 mΩ
 ≤ 5 mΩ ②

-40°C / +75°C ④
 2002/95/EC

| | | | | | | | |
|------------------|-------------------------------|-------------|---|---|----------------------------|------------|---|
| Änd./ rev. index | Änderungs-Nr. / revision code | Datum/ date | Name/ name | gez./ drawn | Datum/ date | Name/ name | Gewicht/ weight [g] |
| | | | | | 04.12.2009 | JA | |
| | | | | gepr./ appr. | 07.12.2009 | BJ | ca./approx. 9,8 |
| | | | Maßstab/ scale | Benennung/ title | | |  |
| e | 29753 | 13.07.2018 | 2:1 | BNC Straight Plug HDTV BNC-Kabelstecker HDTV | | | |
| d | 21419 | 04.12.2009 | untol. Maße/ dim. without tolerances according to | Untert./ doc. type | Zeichnungsnr./ drawing no. | |  Maße/ dimensions: mm Original : DIN A4 Blatt/ sheet 1 von/ of 1 |
| c | 20171 | 08.08.2008 | | K | J01002A0056 | | |
| b | 19495 | 19.11.2007 | | Ersatz für/ replaces | Zeichnung vom 11.07.2005 | | |
| a | 16976 | 07.09.2005 | | | | | |