

## Hydraulic bench-mounted presses



### Version:

- Compact design
- Easy to transport
- Can be used in vertical and horizontal situations in different workplaces
- Appropriate protective measures must be taken for operations where there is the risk of hand injury from the press tool.

### Delivery:

With pump and RC106 pressure cylinder. Ready for operation with 1.8-m hose and manometer.



<b>Art. no.</b>	<b>29769 010</b>
<b>Model</b>	VLP106 P142
<b>Clear width</b>	435 mm
<b>Clear height</b>	430 mm
<b>Compressive force at 700 bar</b>	101 kN
<b>Return stroke design</b>	Spring return
<b>Height</b>	620 mm
<b>Lift height</b>	156 mm
<b>Operating type</b>	Manual