



		A (mm)	B (mm)
E1.443.012	Mac 3	135	18
E1.444.012	Mac 4	155	18

F.O. McCoy Spatel

- Laryngoskop Spatel mit **integrierter Glasfaser**
- das abwinkelbare Spatelende erleichtert schwierige Intubationen und verringert die Verletzungsgefahr
- hochwertige Konstruktion aus Edelstahl für hohe Lebensdauer
- einfache Reinigung oder Sterilisation da keine Schmutznischen
- wartungsfrei
- 8.000 Fasern sorgen für maximale Lebensdauer und Beleuchtungsstärke
- optimale Ausleuchtung durch größtmöglichen Querschnitt (3 x 7 mm)
- Beleuchtungsstärke mit 3.7 V LED: ca. 14.000 Lux
- Beleuchtungsstärke mit 2.5 V Xenon: ca. 6.500 Lux
- kompatibel mit allen Griffen nach ISO 7376 (Grüner Standard)
- autoklavierbar bis 134°C – ca. 4.000 Zyklen
- Data-Matrix mit den wichtigsten Informationen



F.O. McCoy Blade

- laryngoscope blade with **integrated fibre glass**
- facilitates difficult intubation due to movable blade tip and reduce the risk of injury
- high-quality stainless steel construction for a long service life
- no dust collecting cracks – easy cleaning and sterilisation
- maintenance-free
- 8.000 fibres to achieve the maximum service life and illumination
- optimal light emission due to the largest possible cross section (3 x 7 mm)
- brightness approx. 14.000 lux at 3.7 V LED
- brightness approx. 6.500 lux at 2.5 V Xenon
- compatible with all handles according to ISO 7376 (green standard)
- autoclavable up to 134° C – approx. 4.000 times
- Data-Matrix with most important information

