

**TECHNICAL SPECIFICATIONS**

**D-Sub Hood:**



Material: Zinc, Nickel Plated  
 Operating Temperature: -45°C to + 105°C  
 Cable Entry: Top Entry  
 Thumbscrews: UNC 4-40 (Standard)  
 Cable O.D:  
 9-Way: Up to 9,5mm  
 15-Way: Up to 12,5mm  
 25-Way: Up to 12,5mm  
 37-Way: Up to 15,5mm

**Female D-Sub Solder Cup:**

Insulator: PBT, Black, UL94 V-0  
 Shell: Steel, Tin Plated  
 Contact pins: Copper Alloy  
 Stamped & Formed Pins: Class 3, 100 inserts min.  
 Machined Contact Pins: Class 1, 500 inserts min.  
 Contact Plating: Selective Gold over Nickel  
 Operating Temperature: -55°C to +105°C  
 Withstanding voltage: 1000V for 1 minute  
 Insulator resistance: 1000MΩ min.

**Features:**

- Available in sizes 9-15-25-37
- Excellent EMI Shielding
- Re-openable
- Spring-Clip mounted Jackscrews



Size DTZF	Dim A	Dim B	Dim C
9-way	31,6	39,5	15,2
15-way	40,0	41,0	15,2
25-way	53,7	47,5	15,2
37-way	70,2	48,0	15,2

**Ordering information - Black Insulator:**

Size:	P/N - Kitted:	Class 3 - 100 inserts min.
9-way	6355-0044-11	DTZF09-DBS-K
15-way	6355-0044-12	DTZF15-DBS-K
25-way	6355-0044-13	DTZF25-DBS-K
37-way	6355-0044-14	DTZF37-DBS-K

Size:	P/N - Kitted:	Class 1 - 500 inserts min.
9-way	6355-0045-11	DTZF09-DMS-K
15-way	6355-0045-12	DTZF15-DMS-K
25-way	6355-0045-13	DTZF25-DMS-K
37-way	6355-0045-14	DTZF37-DMS-K

**Ordering information - White Insulator:**

Size:	P/N - Kitted:	Class 3 - 100 inserts min.
9-way	6355-8044-11	DTZF09-DBS-W-K
15-way	6355-8044-12	DTZF15-DBS-W-K
25-way	6355-8044-13	DTZF25-DBS-W-K
37-way	6355-8044-14	DTZF37-DBS-W-K

Size:	P/N - Kitted:	Class 1 - 500 inserts min.
9-way	6355-8045-11	DTZF09-DMS-W-K
15-way	6355-8045-12	DTZF15-DMS-W-K
25-way	6355-8045-13	DTZF25-DMS-W-K
37-way	6355-8045-14	DTZF37-DMS-W-K

