



Fixpoint
Cable clip; white

consumption unit 100 x in plastic box



hight				max. cable Ø	nail
5.30 mm	17076	Bulk		4 mm	1.70 x 15 mm
6.30 mm	17077	Bulk		5 mm	1.70 x 15 mm
7.40 mm	17078	Bulk		6 mm	1.85 x 16 mm
8.40 mm	17079	Bulk		7 mm	1.80 x 18 mm
9.40 mm	17080	Bulk		8 mm	1.95 x 19 mm
10.40 mm	17081	Bulk		9 mm	2.05 x 22 mm
11.40 mm	17082	Bulk		10 mm	2.30 x 23 mm
13.40 mm	17083	Bulk		12 mm	2.30 x 25 mm
16.40 mm	17084	Bulk		14 mm	2.35 x 28 mm
17.70 mm	17085	Bulk		16 mm	2.35 x 32 mm



Fixpoint
Cable clip; grey

consumption unit 100 x in plastic box



hight				max. cable Ø	nail
7.40 mm	17122	Bulk		6 mm	1.85 x 16 mm
9.40 mm	17123	Bulk		8 mm	1.95 x 19 mm
11.40 mm	17124	Bulk		10 mm	2.30 x 23 mm
13.40 mm	17125	Bulk		12 mm	2.30 x 25 mm



Fixpoint
Self adhesive mount with eyelet;
natural

for mounting of cable ties up to 3.6 mm

- material: polyamide 6.6 natural acc. to UL 94 V2
self extinguishing, halogene free
- melting point: + 250°C

17104 Bulk