



## Wall Cavity Probe

### P/N: MR06

#### Revision

30133

#### Last modified

2015-10-31 13:02 UTC+1

#### Copyright

© 2018, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

#### Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to [exportquestions@flir.com](mailto:exportquestions@flir.com) with any questions.

#### Website

<http://www.flir.com>

#### Customer support

<http://support.flir.com>



General description	
Part number	MR06
Part name	Wall Cavity Probe
<p>The FLIR MR06 Wall Cavity Probe expands the functionality of your FLIR moisture meter by allowing you to easily measure insulation moisture levels within a wall cavity and the inside face of exterior walls.</p> <p>FLIR's new insulated pins are smaller in diameter—requiring minimal force to drive the pins into a surface—resulting in less impact to the material. The sandblasted, hardened-steel pins with a single-piece design prevent bending and create an improved bonding surface for the abrasion-resistant insulation. The insulation extends all the way to the connection to the probe, so even if you drive the pins all the way into the wall cavity, the drywall will not affect the measurement.</p> <ul style="list-style-type: none"><li>• Insulated pins designed for increased durability.</li><li>• Rubberized ergonomic grips reduce slippage.</li><li>• Detachable cord with a durable BNC connection.</li><li>• Pins included: 1 pair of 4 in. pins, 1 pair of 6 in. pins.</li><li>• Impact plate to drive pins through a drywall.</li></ul>	
Meter data	
Suitable main unit	MR77, MR160, MR176
Cable length	2.45 m (8 ft.) uncoiled
Included insulated pin pairs and length	1 pair of 4 in. (101 mm), 1 pair of 6 in. (152 mm)
Warranty	2 years (with registration)
Meter physical data	
Weight:	0.50 kg (1.10 lb.)
Dimensions (H x W x L)	4.5 cm x 5.97 cm x 28.49 cm (1.8 in. x 2.4 in. x 11.2 in.)
Material	PC-ABS
Color	Black
Shipping information	
Packaging type	Color retail packaging
Packaging contents	MR06, 1 pair 4 in. insulated pins, 1 pair 6 in. insulated pins, cable, impact plate, pin wrench
Packaging weight	0.6 kg (1.3 lb.)
Packaging dimensions (H x W x L)	5.3 cm x 12.3 cm x 19.5 cm (2 in. x 4.9 in. x 7.7 in.)
Master carton weight	11 kg (24.24 lb.)
Master carton dimensions (H x W x L)	24 cm x 28 cm x 44.5 cm (9.5 in. x 11 in. x 17.5 in.)
Master carton quantity	16
EAN-13	0793950370063
UPC-12	793950370063