




## Product information ELWIKA 3008 V

Industrial Connecting Solutions: Circular Connectors: M8 - M12 Connectors: M8 Connectors: M8 Connectors (E series M8): MiniQuick, fast connection, cable socket self-assembled: ELWIKA 3008 V

<http://e-catalog.hirschmann.com/link/57078-24228-256281-256292-256303-276518-24246-37214/en/conf/ui/istate>

|                                     |   |
|-------------------------------------|---|
| Name                                | ELWIKA 3008 V   |
|                                     |  |
|                                     | Angled cable socket, unassembled, strain relief by means of clamping cage         |
| <b>Delivery informations</b>        |   |
| Availability                        | available   |
| <b>Product description</b>          |   |
| Description                         | Angled cable socket, unassembled, strain relief by means of clamping cage         |
| Type                                | ELWIKA 3008 V   |
| Order No.                           | 933 368-100   |
| Type of contact                     | female  |
| Number of contacts                  | 3   |
| Cable gland                         | M 9.5 x 1   |
| Standard                            | IEC 61076-2-101 (Ed. 1)/ IEC 60947-5-2  |
| Housing Color                       | black   |
| <b>Technical data</b>               |   |
| Rated voltage                       | AC/DC 60 V  |
| Rated current                       | 3 A (2 A at 0.14 mm <sup>2</sup> )  |
| Type of termination                 | pin penetration   |
| Suitable cables                     | diameter 4 mm to 5 mm /<br>0.14 mm <sup>2</sup> to 0.34 mm <sup>2</sup>           |
| Core insulation of connecting leads | PVC, PETP,<br>diameter 1.0 mm to 1.55 mm  |
| <b>Material</b>                     |   |
| Contact material                    | Cu Sn   |
| Contact surface material            | Au  |
| Contact bearer material             | PA  |
| Housing material                    | PA  |
| Coupling nut material               | Zn Al/Ni  |
| O-Ring                              | Viton / NBR   |
| <b>Environmental conditions</b>     |   |
| Protection class (IEC 60529)        | IP 67   |
| Pollution severity                  | 3   |
| Temperature range                   | -25 °C to +70 °C  |
| <b>Inflammability class</b>         |   |
| Housing                             | 94 V-2  |
| Contact bearer                      | 94 V-2  |
| <b>Packing unit</b>                 |   |
| Packaging unit                      | 100 pieces  |




# HIRSCHMANN

A BELDEN BRAND

Industrial Connecting Solutions: Circular Connectors: M8 - M12 Connectors: M8 Connectors: M8 Connectors (E series M8): MiniQuick, fast connection, cable socket self-assembled: ELWIKA 3008 V  
<http://e-catalog.hirschmann.com/link/57078-24228-256281-256292-256303-276518-24246-37214/en/conf/ui/state>

## Picture

### Drawing



### Belden Deutschland GmbH

Im Gewerbepark 2  
58579 Schalksmühle  
Germany  
Phone: +49 7127/14-1806  
E-Mail: [icos-sales@belden.com](mailto:icos-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.