

Model Number


V1S-W-2M-PUR

Cable connector, M12, 4-pin, PUR cable

Features

- · Knurled nut suitable for tool assembly
- Immunity to vibration, with mechanical latching
- Gold-plated and machined contacts
- Protection degree IP67 / IP68 / IP69K
- Halogen-free

Dimensions





Technical data

General specifications	
Number of pins	4
Connection 1	Male connector
Construction type 1	right angle
Threading 1	M12
Connection 2	cable end

Electrical specifications

Operating voltage	U_B	max. 250 V AC/DC
Operating current		max. 4 A
Contact resistance		< 10 mΩ

Ambient conditions

	Body: -40 90 °C (-40 194 °F) cable, fixed: -40 80 °C (-40 176 °F) cable, flexing: -25 80 °C (-13 176 °F)
Pollution Degree	3

Pollution Degree

Mechanical specifications

Pin diameter	1 mm
Protection degree	ID67 / ID68 / ID60k

Material

Contacts	CuSn / Au
Contact surface	Au
Body	TPU, black
Cable	PUR
Sleeve connector	Diecast zinc
Core insolation	PP
Cable	fine-strand, flexibl
Sheath diameter	Ø 4.8 mm

Bending radius > 10 x cable diameter, moving > 8 x cable diameter, fixed

Color grey $4 \times 0.34 \text{ mm}^2$ Cores Conductor construction 19 x 0.15 mm Ø

Length 2 m Flammability

94 HB Contact material Housing 94 V-2

Compliance with standards and directives

Standard conformity

Protection degree EN 60529:2000 Standards IEC 61076-2-101:2008

Electrical connection



