


**06/68 Female – JIC 37°
SAE 45° Dual Flare
Swivel – Straight**

ISO12151-5-SWS – DKJ



XXXXX-XX-XX Part Number		Hose I.D.				Thread UNF	A	B	H	W
46	48	DN	Inch	Size	mm		mm	mm	mm	mm
10646-6-4	10648-6-4	6	1/4	-4	6.3	9/16x18	55	31	14	17
16846-4-4	16848-4-4	6	1/4	-4	6.3	7/16x20	52	29	14	17
16846-5-4	16848-5-4	6	1/4	-4	6.3	1/2x20	54	30	14	17
16846-5-4	16848-5-4	6	1/4	-4	6.3	1/2x20	53	30	14	19
10646-6-5	10648-6-5	8	5/16	-5	7.9	9/16x18	56	29	14	17
16846-5-5	16848-5-5	8	5/16	-5	7.9	1/2x20	54	30	14	17
16846-5-5	16848-5-5	8	5/16	-5	7.9	1/2x20	54	30	14	19
16846-8-5	16848-8-5	8	5/16	-5	7.9	3/4x16	57	34	17	22
16846-8-5	16848-8-5	8	5/16	-5	7.9	3/4x16	57	34	17	22
10646-6-6	10648-6-6	10	3/8	-6	9.5	9/16x18	52	30	14	17
16846-4-6	16848-4-6	10	3/8	-6	9.5	7/16x20	50	27	14	17
16846-5-6	16848-5-6	10	3/8	-6	9.5	1/2x20	52	29	14	17
16846-5-6	16848-5-6	10	3/8	-6	9.5	1/2x20	51	29	17	19
16846-8-6	16848-8-6	10	3/8	-6	9.5	3/4x16	56	34	17	22
16846-8-6	16848-8-6	10	3/8	-6	9.5	3/4x16	56	33	17	22
16846-10-6	16848-10-6	10	3/8	-6	9.5	7/8x14	59	36	22	27
10646-6-8	10648-6-8	12	1/2	-8	12.7	9/16x18	55	32	22	19
10646-12-8	10648-12-8	12	1/2	-8	12.7	1-1/16x12	62	38	22	22
16846-8-8	16848-8-8	12	1/2	-8	12.7	3/4x16	56	32	22	27
16846-10-8	16848-10-8	12	1/2	-8	12.7	7/8x14	62	38	27	32
10646-12-10	10648-12-10	16	5/8	-10	15.9	1-1/16x12	64	39	22	22
16846-8-10	16848-8-10	16	5/8	-10	15.9	3/4x16	57	32	22	27
16846-10-10	16848-10-10	16	5/8	-10	15.9	7/8x14	60	35	27	32
10646-12-12	10648-12-12	20	3/4	-12	19.1	1-1/16x12	67	41	24	22
10646-14-12	10648-14-12	20	3/4	-12	19.1	1-3/16x12	68	42	24	27
10646-16-12	10648-16-12	20	3/4	-12	19.1	1-5/16x12	71	45	27	32
16846-8-12	16848-8-12	20	3/4	-12	19.1	3/4x16	58	32	30	36
16846-10-12	16848-10-12	20	3/4	-12	19.1	7/8x14	61	35	32	41
10646-12-16	10648-12-16	25	1	-16	25.4	1-1/16x12	73	44	32	32
10646-16-16	10648-16-16	25	1	-16	25.4	1-5/16x12	76	46	32	41
10646-20-16	10648-20-16	25	1	-16	25.4	1-5/8x12	80	50	41	50
10646-16-20		32	1-1/4	-20	31.8	1-5/16x12	87	49	41	41
	10648-16-20	32	1-1/4	-20	31.8	1-5/16x12	97	50	46	41
10646-20-20		32	1-1/4	-20	31.8	1-5/8x12	89	51	46	50
	10648-20-20	32	1-1/4	-20	31.8	1-5/8x12	100	53	46	50
	10648-24-24	40	1-1/2	-24	38.1	1-7/8x12	98	60	55	60

Approved fitting series for hose types:

Also available in stainless steel. Details can be found in CAT 4400.1/UK

46	or	48	441	441RH	461LT	462	462ST													
46	463	492	492ST	692	692TWIN															
48	301SN	301TC	302	304	351TC	421RH	421SN	421WC	422	426	436	451	451TC	471TC	472TC	477	477ST	493	811	881