



Datasheet for part number DBMC17X2PJ

|   |
|---|
| Our Catalog Part Number: DBMC-17X2P-J                                     |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: COMBO D |

| Product Datasheet               |   |
|---------------------------------|---|
| General                         | Combo D Series: D-Subminiature offering mixed layouts |
| Wire Gauge Range AWG            | AWG 8-26  |
| Mating Cycles                   | 50  |
| Contact Arrangement             | 17X2 (15 contacts size 20, 2 contacts size 8)         |
| Dielectric Withstanding Voltage | 500 VAC at sea level                                  |
| Current Rating Signal Contacts  | 7.5 max   |
| Current Rating Size 8 Contacts  | 5 A max   |
| Contact Resistance              | 10 milli Ohm max                                      |
| Operating Temperature           | -55°/+125°  |
| Salt Spray Test                 | 20 hours  |
| Shell Material                  | steel   |
| Shell Finish                    | Yellow chromate over zinc                             |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0                      |
| Insulator Color                 | black   |
| Gender                          | Pin   |
| Contact Type                    | Right angle US footprint                              |
| Contact Material                | copper alloy  |
| Contact Finish                  | gold flash (Performance Class 3)                      |
| Mounting Method                 | 90° Metal Bracket, 4-40 Fastener & Boardlock          |