


Product information

38 91 200

Mechanics' Pliers


DIN ISO 5745

- High bending strength of the pliers tips
- Gripping surfaces cross-hatched, knurled
- 45° angled, half-round, long jaws, also suitable for gripping spark plugs and round components (spark plug cover "grabber")
- Vanadium electric steel; forged, oil-hardened



General	
Article No.	38 91 200
EAN	4003773017219
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	177 g
Dimensions	200 x 51 x 13 mm
Standard	DIN ISO 5745
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Jaw thickness (joint) (T1)	9.5 mm
Tips thickness (T2)	2.5 mm
Jaw length (L3)	73.0 mm
Head width (W3)	17.5 mm
Head angle	45 °



technical change and errors excepted

