



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER: **R284C0351026**

Issue : **NA**

Date : **NA**


Customer : **Radio Spares**

Specification : **NA**

Issue : **NA**

Date : **N/A**

All dimensions are in mm



Connectors designation :

**Connector 1 : BNC Straight Plug Crimp Type
Cable 5/50 S (R141.082.161)**

**Connector 2 : N Straight Plug Full Crimp Type
Cable 5/50 S (R161.082.000)**

Cable designation :

**Flexible Cable 5/50S (RG58)
C291.305.000
Lg: 500 mm**

Nominal length :

Cable colour :

**Black
4.95 mm**

Outer diameter :

Accessories :

Plastic Boots (R280.570.000)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : **50±2 Ohms**

Frequency range : **DC-1GHz**

Insertion Loss : **0.55dB max. @ 1GHz & 20 °C**

VSWR. : **NA**

Low Frequency

Insulation Resistance : **5000M Ohms min.**

Voltage Rating : **500 Veff max**

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : **20 mm**

Cable crush resistance : **NA**

Life (connectors) : **100 cycles**

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : **-35° C to +70° C**

Remark : **NA**

Attachment : **R141.082.161-TDS , R161.082.000-TDS**

C291.305.000 (RG58)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

**Service or
Company's stamp**

**Name
Date**

| | | | | |
|-------|-------|-----------|--------------|------------|
| Peter | A | 2007-5-25 | Creation | Willy |
| Name | Issue | Date | Modification | Checked by |



No.390, Yong He Road,
Shanghai 200072, China

TECHNICAL DATA SHEET CABLE ASSEMBLY

PART NUMBER: **R284C0351027**

Issue : **NA**

Date : **NA**


Customer : **Radio Spares**

Specification : **NA**

Issue : **NA**

Date : **N/A**

All dimensions are in mm



Connectors designation :

**Connector 1 : BNC Straight Plug Crimp Type
Cable 5/50 S (R141.082.161)**

**Connector 2 : N Straight Plug Full Crimp Type
Cable 5/50 S (R161.082.000)**

Cable designation :

**Flexible Cable 5/50S (RG58)
C291.305.000**

Nominal length :

Lg: 1000 mm

Cable colour :

Black

Outer diameter :

4.95 mm

Accessories :

Plastic Boots (R280.570.000)

ELECTRICAL CHARACTERISTICS :

High Frequency

Characteristic impedance : **50±2 Ohms**

Frequency range : **DC-1GHz**

Insertion Loss : **1.01dB max. @ 1GHz & 20 °C**

VSWR. : **NA**

Low Frequency

Insulation Resistance : **5000M Ohms min.**

Voltage Rating : **500 Veff max**

MECHANICAL CHARACTERISTICS :

Recommend min. bend radius : **20 mm**

Cable crush resistance : **NA**

Life (connectors) : **100 cycles**

ENVIRONMENTAL CHARACTERISTICS :

Operating temperature range : **-35° C to +70° C**

Remark : **NA**

Attachment : **R141.082.161-TDS , R161.082.000-TDS**

C291.305.000 (RG58)-TDS

Cable Assembly is RoHS compliant.

CUSTOMER'S APPROVAL

**Service or
Company's stamp**

Name

Date

| | | | | |
|-------|-------|-----------|--------------|------------|
| Peter | A | 2007-5-25 | Creation | Willy |
| Name | Issue | Date | Modification | Checked by |