



Main

Range	Spacial
Product name	Spacial S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	19.69 in (500 mm)
Enclosure nominal width	15.75 in (400 mm)
Enclosure nominal depth	7.87 in (200 mm)
Door type	Solid
Mounting plate description	Plain
Type of gland plate	Standard
Installation accessory type	Wall-mounting
Device composition	1 body 1 mounting plate 1 door with lock 1 cable gland plate

Complementary

Body type	Single piece body Gutter-shaped front rail double sheet thickness
Number of doors	Front face 1
Door opening side	Reversible (120 °)
Lock type	3 mm double-bar lock
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Enclosure steel Mounting plate galvanised steel
Surface finish	Enclosure epoxy-polyester powder
Color	Enclosure Gray RAL 7035)
Standards	IEC 62208
Product certifications	UL CUL GL LR DNV BV
Net Weight	23.28 lb(US) (10.56 kg)

Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	03606480159442
Nbr. of units in pkg.	1
Package weight(Lbs)	24.2 lb(US) (10.98 kg)
Returnability	No
Country of origin	FR

Packing Units

Package 1 Height	20.28 in (515.000 mm)
Package 1 width	16.54 in (420.000 mm)
Package 1 Length	9.65 in (245.000 mm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------