



GE  
Lighting

## 21613 - FXL

GE Quartzline® Multi-Mirror® MR16 - Overhead Projection



### GENERAL CHARACTERISTICS

Lamp Type	Halogen - MR
Bulb	MR16
Base	Miniature 2-Pin (GY5.3)
Filament	CC-8
Rated Life	38.0 hrs
Typical Lamp Working Distance	11.75 in
Primary Application	Overhead Projection

### PHOTOMETRIC CHARACTERISTICS

Color Temperature	3300.0 K
-------------------	----------

### ELECTRICAL CHARACTERISTICS


Wattage	410.0
Voltage	82.0
Burn Position	Horizontal ±15° or Base Down

### DIMENSIONS

Maximum Overall Length (MOL)	1.7500 in(44.4 mm)
Bulb Diameter (DIA)	2.000 in(50.8 mm)

### PRODUCT INFORMATION

Product Code	21613
Description	FXL
ANSI Code	FXL
Standard Package	BUNDLE
Standard Package GTIN	00043168216135
Standard Package Quantity	20
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	20
UPC	043168994323



### CAUTIONS & WARNINGS

#### Caution

- Risk of Burn
  - Allow lamp/fixture to cool before handling.
  - Turn power off before installing lamp.
- Lamp may shatter and cause injury if broken
  - Dispose of lamp in a closed container.
  - Do not use lamp if outer glass is scratched or broken.

#### Warning

- Risk of Electric Shock
  - Turn power off before inspection, installation or removal.
- Risk of Fire
  - Keep combustible materials away from lamp.
  - Use in enclosed fixture rated for this product.
- Pressurized lamp--unexpected rupture may cause injury, fire, or property damage
  - Avoid direct water, liquid or metal contact.
  - Do not exceed 110% of rated voltage.
  - Do not use lamp if outer glass is scratched or broken.
  - Use in enclosed fixture rated for this product.