


DURACELL®

Lithium/Manganese Dioxide Battery

DL1/3N

Li/MnO₂




Dimensions shown are IEC/ANSI standards

Nominal Voltage:	3.0 V
Typical Voltage:	3.0-3.3 V
Nominal Internal Impedance:	250 m-ohm @ 1kHz
Average Weight:	3 gm
Volume:	1.1 cm ³
Terminals:	Flat, cap and base
Operating Temperature Range:	-20°C to 60°C (-4°F to 140°F)
ANSI:	5008LC
IEC:	CR11108

Preliminary

DL1/3N Discharge Load vs Capacity to 2.0 volts



DURACELL®

BATTERIES

Berkshire Corporate Park
Bethel, CT 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
Internet: www.duracell.com

* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.