

MILAN S.r.l. a socio unico

Head Office – Export department:

Viale Europa, 74
20090 Cusago (MI) Italy
T. +39 02 9039.4556-4158
F. +39 02 9039.4551
www.taskercables.com

Ufficio Commerciale e Centro Distribuzione

Viale Europa 72 Strada F12
20090 Cusago (MI) Italy
T. +39 02 9039.0037-0059
F. +39 02 9039.0049
www.tasker.it

Technical Datasheet


RoHS₂
 2002/95/EC
 2011/65/UE

tasker® TSK51 – 2x0,50 mm²

Flat Audio Divisible Cable



A	B
---	---

CATEGORY Flat Cable (See Audio Catalogue)
APPLICATIONS Speaker and Home Theatre installation

- A:** Red and Black Soft **PVC** Sheath.
Outer cable dimension 2,20x4,40 (±0,10) mm.
- B:** Both conductors in CCA - Formation with 0,20 mm wires.
Nominal cross section 2x0,50 mm².

CUSTOM PRODUCTION This product may be custom produced also in **L.S.Z.H.** polymer, **PE** or **PUR**.

Cable Properties

Conductor Resistance	45 Ω/Km
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego		Outdoor Limited	Esterno Limitato	Posa	X	Restricted Mobile	Mobile Limitata	Informazioni	X	Ver. A / 16.05.16
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			