


B2 Female BSP Parallel Pipe Swivel 90° Elbow (60° Cone)

BS 5200-B – DKR 90°



XXXXX-XX-XX Part Number		Hose I.D.				Thread BSP	A	B	E	W
46	48	DN	Inch	Size	mm		mm	mm	mm	mm
1B246-2-4	1B248-2-4	6	1/4	-4	6.3	1/8x28	50	26	30	14
1B246-4-4	1B248-4-4	6	1/4	-4	6.3	1/4x19	50	26	28	19
1B246-6-4	1B248-6-4	6	1/4	-4	6.3	3/8x19	51	27	27	22
1B246-8-4	1B248-8-4	6	1/4	-4	6.3	1/2x14	51	27	29	27
1B246-6-5	1B248-6-5	8	5/16	-5	7.9	3/8x19	52	28	28	22
1B246-6-6	1B248-6-6	10	3/8	-6	9.5	3/8x19	61	38	33	22
1B246-8-6	1B248-8-6	10	3/8	-6	9.5	1/2x14	60	38	36	27
1B246-6-8	1B248-6-8	12	1/2	-8	12.7	3/8x19	63	40	41	22
1B246-8-8	1B248-8-8	12	1/2	-8	12.7	1/2x14	63	40	41	27
1B246-10-8	1B248-10-8	12	1/2	-8	12.7	5/8x14	67	43	39	30
1B246-10-10	1B248-10-10	16	5/8	-10	15.9	5/8x14	70	45	44	30
1B246-12-10	1B248-12-10	16	5/8	-10	15.9	3/4x14	70	45	42	32
1B246-12-12	1B248-12-12	20	3/4	-12	19.1	3/4x14	80	54	53	32
1B246-16-12	1B248-16-12	20	3/4	-12	19.1	1x11	80	54	54	41
1B246-16-16	1B248-16-16	25	1	-16	25.4	1x11	104	75	69	41
1B246-20-20		32	1-1/4	-20	31.8	1-1/4x11	124	86	76	50
	1B248-20-20	32	1-1/4	-20	31.8	1-1/4x11	130	82	76	50
	1B248-24-24	40	1-1/2	-24	38.1	1-1/2x11	140	102	103	55
	1B248-32-32	50	2	-32	50.8	2x11	185	137	134	70

Approved **fitting series** for hose types:

Also available in stainless steel. Details can be found in CAT 4400.1/UK

46	or	48	441	441RH	461LT	462	462ST													
46	463	492	492ST	692	692TWIN															
48	301SN	301TC	302	304	351TC	421RH	421SN	421WC	422	426	436	451	451TC	471TC	472TC	477	477ST	493	811	881