














Junction boxes, COMBI 108



COMBI 108



Protection class: IP 66
Glow wire test: 750 °C
Temperature range: -25 °C - 50 °C
Installation temperature: -5 °C - 60 °C
Voltage: 400 V
Terminals/poles: 2,5 mm²
Advice: Colour: RAL 7035 · .../S = RAL 9005 · .../W = RAL 9001 · .../DR = RAL 7035 / RAL 3000 · .../SMB = mounting clip
Material: Polypropylene, Gasket: TPE

Type	WISKA-No.	 (mm)		LxBxH external (mm)	
COMBI 108/empty	10060522	3 · 14		76 x 76 x 51	10
COMBI 108/empty/S	10061999	3 · 14		76 x 76 x 51	10
COMBI 108/empty/W	10060622	3 · 14		76 x 76 x 51	10
COMBI 108/empty/DR	10060632	3 · 14		76 x 76 x 51	10
COMBI 108/empty/SMB	10061974	3 · 14		76 x 76 x 51	10
COMBI 108/5	10060523	3 · 14		76 x 76 x 51	10
COMBI 108/5/S	10061998	3 · 14		76 x 76 x 51	10
COMBI 108/5/W	10060623	3 · 14		76 x 76 x 51	10
DIN RAIL KIT 308/108	10060362	-	-	-	1

POLYAMIDE
POLYAMIDE ACCESSORIES
MEMBRANE
BRASS
BRASS ACCESSORIES
MARITIME
STAINLESS STEEL
EMC
EX E / I
EX D
VENTING
BS 6121
SEALINGS, TOOLS
JUNCTION BOXES
TECHNICS
INDEX