

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2147612215](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Micro-Fit 3.0 Female-to-Pigtail, Gold (Au) Plated, 450.00mm Length, 20 AWG, Red

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	214761
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Micro-Fit 3.0 Crimp Terminals
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	Micro-Fit 3.0
UPC	193264574667

Physical

Cable Length	450.00mm
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female-Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	3.158/g
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	20
Wire/Cable Type	UL 10002

Electrical

Current - Maximum per Contact	8.5A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Sales Drawing	2147611211-000
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[214761](#) Series

Use With

Micro-Fit 3.0 Receptacle Housings [43025](#)
, [43645](#)
Micro-Fit BMI Panel Mount
Receptacle Housings [44133](#) , [46623](#)