

PG/PG-Length Nylon Cable Glands with Strain Relief

multicomp PRO

**RoHS
Compliant**




Specifications

Material	: PA (Nylon), UL 94 V-2
Hermetic Seal	: NBR
O-Ring	: EPDM
Working Temperature	: -40°C to 100°C in static state Instantaneous heat resistance up to 120°C -20°C to 80°C in dynamic state Instantaneous heat resistance up to 100°C
Colour	: Grey and Black
IP Rating	: IP68



Dimensions



Part Number	Thread ØD1	∅k mm	H mm	GL mm	d mm	U mm
PP001688	PG7	3-6.5	54	8	7	16.5/15
PP001689	PG9	4-8	63	8	8.5	19
PP001690	PG11	5-10	78	8	10.5	22
PP001691	PG13.5	6-12	90	9	13	24
PP001692	PG16	10-14	100	10	15.5	27
PP001693	PG21	13-18	114	11	20	33
PP001694	PG7	3-6.5	54	8	7	16.5/15
PP001695	PG9	4-8	63	8	8.5	19
PP001696	PG11	5-10	78	8	10.5	22
PP001697	PG13.5	6-12	90	9	13	24
PP001698	PG16	10-14	100	10	15.5	27
PP001699	PG21	13-18	114	11	20	33

Part Number Table

Description	Colour	Part Number
Nylon Cable Glands with Strain Relief, PG7, 3-6.5mm	Black	PP001688
Nylon Cable Glands with Strain Relief, PG9, 4-8mm		PP001689
Nylon Cable Glands with Strain Relief, PG11, 5-10mm		PP001690
Nylon Cable Glands with Strain Relief, PG13.5, 6-12mm		PP001691
Nylon Cable Glands with Strain Relief, PG16, 10-14mm		PP001692
Nylon Cable Glands with Strain Relief, PG21, 13-18mm		PP001693

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

PG/PG-Length Nylon Cable Glands with Strain Relief

multicomp PRO

Description	Colour	Part Number
Nylon Cable Glands with Strain Relief, PG7, 3-6.5mm	Grey	PP001694
Nylon Cable Glands with Strain Relief, PG9, 4-8mm		PP001695
Nylon Cable Glands with Strain Relief, PG11, 5-10mm		PP001696
Nylon Cable Glands with Strain Relief, PG13.5, 6-12mm		PP001697
Nylon Cable Glands with Strain Relief, PG16, 10-14mm		PP001698
Nylon Cable Glands with Strain Relief, PG21, 13-18mm		PP001699

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO