



Junction boxes, COMBI 1010



COMBI 1010



Protection class: IP 66 / 67
Glow wire test: 750 °C
Temperature range: -30 °C - 100 °C
Installation temperature: -5 °C - 60 °C
Voltage: 690 V
Terminals/poles: 10 mm²
Advice: 10 knockouts 5x M 25/32, 2x M 20, 3x M 20/25, Colour: RAL 7035 - .../S = RAL 9005 - .../W = RAL 9001
Material: Polypropylene, Gasket: TPE

Type	WISKA-No.		LxBxH external (mm)	
COMBI 1010/empty	10060702		140 x 140 x 82	2
COMBI 1010/empty/S	10062214		140 x 140 x 82	2
COMBI 1010/empty/W	10062210		140 x 140 x 82	2
COMBI 1010/5	10060703		140 x 140 x 82	2
COMBI 1010/5/S	10062215		140 x 140 x 82	2
COMBI 1010/5/W	10062211		140 x 140 x 82	2
DIN RAIL KIT 1010	10060363			1