

382A012 to 046


Y transition




Applications

Provides strain relief and mechanical protection on cable harness assemblies.

As supplied (a)



After unrestricted recovery (b)



Available in:

Americas

Europe

Asia Pacific



Fax-on-demand

US only (800) 260-9099

Outside US (650) 257-2301

Fax ID

3422

Description

SCD

Visit our website at www.tycoelectronics.com**Materials available**

| Material* | Material description | Precoating no. | Adhesive part no.** |
|-----------|---------------------------|---|----------------------------|
| -3 | Semirigid polyolefin | /42 or /86 | S-1017 or S-1048 |
| -4 | Flexible polyolefin | /42 or /86 | S-1017 or S-1048 |
| -12 | Viton | N/A | S-1255-04 |
| -25 | Fluid-resistant elastomer | /42 or /86 or /225 | S-1017 or S-1048 or S-1125 |
| -100 | Polyolefin, Zerohal | -100-CS1972 (S1030 tape supplied in bag) | S-1030 |

*For more information, please see the appropriate material page in this section.

**For more information, please see Section 5 of this catalog.

Product dimensions (mm/in)

| Part number | H | | J & K | | S | T | HW | JW & KW |
|-------------|-------------|-------------|-------------|------------|--------------|-------------|------------|------------|
| | Min. a | Max. b | Min. a | Max. b | ±10% b | ±10% b | ±20% b | ±20% b |
| 382A012 | 13.2 (.52) | 6.1 (.24) | 6.6 (.26) | 3.3 (.13) | 23.9 (.94) | 15.5 (.61) | 1.52 (.06) | 1.02 (.04) |
| 382A023 | 26.9 (1.06) | 12.4 (.49) | 13.2 (.52) | 6.1 (.24) | 53.3 (2.10) | 33.0 (1.30) | 2.54 (.10) | 1.52 (.06) |
| 382A034 | 38.6 (1.52) | 18.0 (.71) | 26.9 (1.06) | 12.4 (.49) | 78.7 (3.10) | 55.9 (2.20) | 3.05 (.12) | 2.54 (.10) |
| 382A046 | 55.6 (2.19) | 25.9 (1.02) | 26.9 (1.06) | 12.7 (.50) | 111.8 (4.40) | 71.1 (2.80) | 4.57 (.18) | 2.54 (.10) |

Note: Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5 mm (.06") max.