

Resisto SylSmart

Resisto 1200 HE IP65 2800lm 840 SSE

0010238



Product features

- Resisto, integrated LED weatherproof luminaire, with UV stabilized flat diffuser designed to achieve uniform lit appearance, optimise light output and to reduce glare. 301 stainless steel diffuser clips and fixing brackets for surface mounting. Polycarbonate housing and diffuser - no yellow discolouration over time. 2800lm; 20W; 140lm/W; 4000K; SDCM<5; CRI80; IP66; IK08 (sensor IK03); Class I; 69,000hrs (L80B20) lifespan; 1293mm x 87mm x 80mm; D-mark; SylSmart Connected Industry enabled.



PRODUCT OVERVIEW

Product name	Resisto 1200 HE IP65 2800lm 840 SSE
Technology	LED
Cap/Base	N/A
Housing	PC Polycarbonate
Mount	Ceiling surface mounting, Suspended, Wall surface mounted
General application	Logistics & Industry
ETIM Class	EC002892
Warranty	5 years
Fixture luminous flux (lm)	2800
Luminaire efficacy (lm/W)	140
Colour temperature (K)	4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Colour Consistency (SDCM)	3
Beam Angle (°)	110
Glare control	< 22
Photobiological Risk Group	RG1
Total power consumption (W)	20
Electrical protection	Class I
Control gear type	LED driver constant current
Dimmable	Yes
Dimming method	SylSmart SSE
Minimum dimming level (%)	1
LED Flickering Rate	Ultra low (5% or less)
Housing colour	Grey
IP rating	IP65
IK rating	IK08
Product EAN number	5410288102382

DATA TABLE

General data

Product name	Resisto 1200 HE IP65 2800lm 840 SSE
--------------	-------------------------------------

Resisto SylSmart

Resisto 1200 HE IP65 2800lm 840 SSE

0010238

Technology	LED
Cap/Base	N/A
Housing	PC Polycarbonate
Mount	Ceiling surface mounting, Suspended, Wall surface mounted
General application	Logistics & Industry
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
Warranty	5 years

Optical data

Fixture luminous flux (lm)	2800
Luminaire efficacy (lm/W)	140
Colour temperature (K)	4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Colour Consistency (SDCM)	3
Beam Angle (°)	110
Distribution type	Diffuse
Glare control	< 22
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	20
Mains voltage (V)	220-240V
Lamp power factor	0.95
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	10
Electrical protection	Class I
Control gear required	No
Control gear type	LED driver constant current
No. Of switching cycles before premature failures	>50000
Transformer required	No
Dimmable	Yes
Dimming method	SylSmart SSE
Minimum dimming level (%)	1
Drive current (mA)	350
Inrush Current (A)	30
Inrush Duration (µs)	200
Glow Wire Test (°C)	850
Energy Efficiency Class (A->G) of contained light source	C
Nominal Frequency (Hz)	50/60Hz
LED Flickering Rate	Ultra low (5% or less)
Max. Luminaires per 10A B Breaker	10
Max. Luminaires per 16A B Breaker	16

Lifetime data

Resisto SylSmart

Resisto 1200 HE IP65 2800lm 840 SSE

0010238

Lifespan L70 B50	100000
Lifespan L80 B20	69000
Lifespan L90 B10	31000

Physical data

Housing colour	Grey
IP rating	IP65
IK rating	IK08
IK rating of sensor	IK03
Diffuser finish	Frosted
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	1293
Nominal Product Width (mm)	87
Nominal Product Height (mm)	80
Weight (kg)	1.53

Packaging

Single packaging type	Carton
Product EAN number	5410288102382
Packaging single length / height (cm)	120.5
Packaging single width (cm)	10.0
Packaging single depth (cm)	8.5
DUN14 (outer)	05410288102382
Units per outer package	1
Packaging outer length / height (cm)	120.5
Packaging outer width (cm)	10.0
Packaging outer depth (cm)	8.5


Safety data

Optimal operating condition (°C)	-20-40
----------------------------------	--------

PHOTOMETRY

Distance [m]	Cone diameter [m]	E(0°)	E(C90)	E(C0)	Illuminance [lx]
0.5	1.30 1.38	3661	416	374	
1.0	2.61 2.75	920	104	94	
1.5	3.91 4.13	409	46	42	
2.0	5.21 5.51	230	26	23	
2.5	6.52 6.88	147	17	15	
3.0	7.82 8.26	102	12	10	

Distance [m] Cone diameter [m] Illuminance [lx]
 — C0 - C180 (Half beam angle: 105.0°)
 — C90 - C270 (Half beam angle: 105.0°)



Resisto SylSmart

Resisto 1200 HE IP65 2800lm 840 SSE

0010238

TECHNICAL DRAWINGS

