

RefLED Retro Superia ES50 DIMMABLE

RefLED Sup RT ES50 V2 450 DIM 827 36d SL

0028555



Product features

- Premium performance professional LED GU10 range with the same look and feel of traditional halogen GU10 lamp
- Recreates backlight effect similar to halogen dichroic lamps
- Full glass design - means no colours clashing between lamp and fixture
- Very long lifetime of up to 25,000 hours
- COOLFIT functionality - ensures overheat and over temperature protection
- High switching cycles: >100,000
- High colour rendering: CRI80
- Dimmable on approved dimmers
- Warranty: 5 Years



PRODUCT OVERVIEW

Product name	RefLED Sup RT ES50 V2 450 DIM 827 36d SL
Technology	LED
Watt (Rated) (W)	5
Cap/Base	GU10
Fixture rating	Open
General application	Education, Hospitality, Museums & Galleries, Office, Residential & Consumer, Retail
ETIM Class	EC001959
E-number FI	4740852
Warranty	5 years
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Colour Consistency (SDCM)	6
Colour Variation Initial (SDCM)	SDCM6
Beam Angle (°)	36
Wattage (W)	5
Product Voltage (V)	230
Average life (Nominal) (h)	25000
Product EAN number	5410288285559

DATA TABLE

General data

Product name	RefLED Sup RT ES50 V2 450 DIM 827 36d SL
Technology	LED
Watt (Rated) (W)	5
Cap/Base	GU10
Fixture rating	Open
General application	Education, Hospitality, Museums & Galleries, Office, Residential & Consumer, Retail
Performance ambient temperature Tq (°C)	25

RefLED Retro Superia ES50 DIMMABLE

RefLED Sup RT ES50 V2 450 DIM 827 36d SL
0028555

ETIM Class	EC001959
E-number FI	4740852
Warranty	5 years

Optical data

Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Colour Consistency (SDCM)	6
Colour Variation Initial (SDCM)	SDCM6
Luminous Intensity (cd)	800
Beam Angle (°)	36
Lumen maintenance at end of nominal life (%)	70

Electrical data

Wattage (W)	5
Equivalent watt (W)	64
Starting time (max) (s)	<0.5
Warm-up time to 60% of full light (max) (s)	<1
Product Voltage (V)	230
Lamp power factor	0.7
No. Of switching cycles before premature failures	>100000
Inrush Current (A)	0.46
Nominal Frequency (Hz)	50Hz
Max. Luminaires per 10A C Breaker	87
Max. Luminaires per 16A C Breaker	140
Max. Luminaires per 20A C Breaker	175

Lifetime data

Average life (Nominal) (h)	25000
Average life (Rated) (h)	25000

Physical data

Nominal Product Length (mm)	54
Nominal Product Diameter (mm)	50
Weight (kg)	0.055

Packaging

Single packaging type	Carton
Product EAN number	5410288285559
Packaging single length / height (cm)	6.7
Packaging single width (cm)	5.1
Packaging single depth (cm)	5.1
DUN14 (inner)	25410288285553
Units per inner package	6
Packaging inner length / height (cm)	7.5
Packaging inner width (cm)	16.5

RefLED Retro Superia ES50 DIMMABLE

RefLED Sup RT ES50 V2 450 DIM 827 36d SL
0028555

Packaging inner depth (cm)	11.0
DUN14 (outer)	15410288285556
Units per outer package	60
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	58.0
Packaging outer depth (cm)	17.8

Safety data

Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Dimmable with approved dimmers

PHOTOMETRY

