

Knurling tool (series RD2 model 141)

for knurl pressing on lathes and turning machines



Application:

For knurl forming for knurl profiles in accordance with DIN 82 RAA, RBL30°/45°, RBR30°/45°, RGE 30° and RGE 45° in the steel, stainless steel and non-ferrous metals material groups.

Execution:

- Hardened steel tool holder, integrated tip height, cemented carbide runner pins

Advantage:

- click-pin design for user-friendly handling (only with 20x20 and 25x20 shaft designs)
- modular design enables right-handed and left-handed knurl forming
- Inexpensive knurl production
- Flexible centring and adjustable clearance angle



Art. no.	19005 016
Brand	ZEUS
Manufacturer Part Number	31002658
Suitable for knurling size	15 x 4 x 4 mm
Shank width	16 mm
Shaft height	16 mm
For min./max. workpiece diameter	6-60 mm
Gross Weight	0.320 kg
Product Group	1FP