

Electronic outside micrometer

small measuring faces

Mitutoyo

Application:

For measuring narrow external recesses and grooves.

Execution:

- Carbide-tipped measuring faces
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)
- Non-rotating spindle
- IP65
- Digimatic

Advantage:

- Accesses hard-to-reach measuring points

Delivery:

Includes box, set standard (25 mm or more), adjustment wrench, battery



Art. no.	32017 538
Brand	MITUTOYO
Manufacturer Part Number	331-354-30
Display	Digital
Min./max. length measuring range in inches	3-4 in
Digit increment	0.00005 in
Measuring surface diameter	3 mm
IP protection class	IP 65
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Origin (Dimension preset), Hold-function (AE lock), Automatic switch-off
Min./max. measurement force	5-10 N
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Bracket depth	76 mm
Measuring spindle increments	0.5 mm
Calibration Group	D
Gross Weight	1.285 kg
Product Group	3MA

EAN

4946368688916