

Data Sheet

15-Pin D-sub terminal connector modular



T1904C092 - Male connector with jackscrew nut connection



T1904C093 - Female connector with jackscrew nut connection



T1904C094 - Male connector with locking screw connection






T1904C095 - Female connector with locking screw connection

Included accessories
 1x Screw driver
 1x Cable strain Relief
 2x Fastening screw




Material:
 Housing: PP
 Connector insulator: PBT+30%GF (UL94V-0)
 Contact: Brass
 Contact plated: Nickel
 Connector shell plated: Cu60µ/Ni100-120µ
 Technical:
 Contact current rating: 5A max.
 Insulation resistance: 1000MΩ min. at 500V/DC
 Dielectric withstanding voltage: 500V/AC(R.M.S)/1min.
 Operation temperature: -20 ~85°C



Male

- 1 RSSI analog input
- 2 Enable switch input
- 3 Tach signal input
- 4 Heading switch input
- 5 IrDA output
- 6 RS232 output
- 7 -V inout
- 8 +DC input
- 9 Squeal tone output
- 10 Ground
- 11 Ground
- 12 Ground
- 13 Ground
- 14 Ground
- 15 +DC



Female