

Data sheet for Line filter

Article No. : 6SL3203-0BE23-5HA0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Input

Number of phases	3 AC
Line voltage	200 ... 480 V

Output

Rated current	35.0 A
---------------	--------

Mechanical data

Degree of protection	IP20 / UL open type
Net weight	2.30 kg (5.07 lb)

Dimensions

Width	50.0 mm (1.97 in)
Height	296.2 mm (11.66 in)
Depth	220.0 mm (8.66 in)

Connections

Line side

Version	screw-type terminal
Conductor cross-section	0.50 ... 10.00 mm ² (AWG 21 ... AWG 8)

Load side

Version	Screw-type terminals
Conductor cross-section	16.00 mm ² (AWG 6)

PE connection

Version	M4 screw studs
---------	----------------

Standards

Compliance with standards	CE, cURus, EAC
---------------------------	----------------