

ABS-236-RC SPEAKER

SPEAKERS

Specifications


ABS-236-RC

Rated impedance	8±15%Ω
Rated power	2.0W
Maximum power	4.0W
Resonant frequency	550±20%Hz
Frequency range	F 0-8Khz
Sound pressure level at 2.0W/0.1M	100±3dB
Operating temperature	-30°C~+70°C
Storage temperature	-40°C~+80°C
Weight	55g
Cone material	Paper and Cloth
Magnet size	Dia 12.5x2.5
Magnet material	Nd-Fe-B
Lead wire	UL1007 AWG26
Connector	XH-2P

Features

- ROHS compliant
- High handling capacity
- High power

All data at 25°C unless otherwise specified



Dimensions Unit: mm



Alan Butcher Components

Alan Butcher Components Ltd

Unit 1 Beechwood Clump Farm Industrial Estate Tin Pot Lane Blandford Dorset DT11 7TD


Telephone 01258 456360 Email sales@abcomponents.co.uk

www.abcomponents.co.uk

ABS-236-RC SPEAKER - Frequency Curve

SPEAKERS

0.1m 2W 4V



Alan Butcher Components

Alan Butcher Components Ltd
Unit 1 Beechwood Clump Farm Industrial Estate Tin Pot Lane Blandford Dorset DT11 7TD
Telephone 01258 456360 Email sales@abcomponents.co.uk
www.abcomponents.co.uk