


CUBE20S POWER MODULE

24VDC + 5VDC/2A

Power module
Expansion module
for external voltage supply and internal backplane

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals



Technical Data

Operating voltage	max. 28.8 V DC
Total current	max. 10 A

General data

Protection	IP20
Connection	Spring clamp terminals: 0.08...2.5 mm ² (AWG 28...12)
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+60 °C (storage temperature -25...+70 °C)
Dimensions H × W × D	109×12.9×76.5 mm

Output

Output current (I/Os /Backplane)	4 A/2 A
Output voltage (I/Os /Backplane)	24 V DC/5 V DC

Module Supply

Operating voltage	max. 28.8 V DC
Total current	max. 6 A

Commercial data

country of origin	TH
customs tariff number	85369010
minimum order quantity	1