



Toggle switches

9043.0101

Product number	9043.0101	
Business unit	Switches, Sensors & Controls	
Product family	Toggle switches	
Actuation type	direct	
Packing unit		100
ROHS conform	yes	
Switching function	Changeover switch with OFF position in the center (SPDT - Center OFF)	
Material fixed contact	Ag	
Contact system	Electrical life	50000
Number of poles	1 - pole	
connections	Solder terminal, sealed	
Mechanical life endurance		100000
Rating IEC	4 A 30 V DC	
	5 A 48 V AC	
Contact resistance (new condition)	< 20 mOhm	
Insulation resistance (new condition)	> 1000 MOhm	
Voltage strength at 250 V	small contact distance	> 1000 V
Ambient temperature	-25 °C ... +70 °C	
Actuators and additional actuators	lever: CuZn chrome-plated	
Housing description	bracket plate: stainless steel	
	base plate: DAP, olivegreen	
	threaded socket: CuZn nickel-plated, hexagonal nuts of nickel-plated CuZn	
Connection surface	bearing connection	silver plated
	external connection	silver plated
Contact material	Ag	
Contact type	lifting contact	
Miscellaneous	locking ring and toothed washer of galvanised and chromated steel / momentary function both sides	
Type of fastening	central fastening M6 x 0.75	

Technical changes reserved. Dimensions are not binding.

Detailed specifications available on request.