


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0334670006](#)
Status: **Active**
Overview: MX64 Sealed Connectors
Description: 2.54mm Pitch MX64 Terminal, Gold (Au) Plating, 18-20 AWG, Left Reel Payoff, Also used with MX123 Female Receptacle Housing

Documents:

Drawing (PDF)	Packaging Specification PK-30907-759 (PDF)
Product Specification PS-33468-001-001 (PDF)	Packaging Specification PK-31300-516 (PDF)
Application Specification AS-33468-001-001 (PDF)	Packaging Specification PK-31302-480 (PDF)
Packaging Specification 313025040-000 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Terminals
Series	33467
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Left Reel Payoff
Crimp Quality Equipment	Yes
Overview	MX64 Sealed Connectors
Product Name	MX123, MX64
UPC	756054763391

Physical

Gender	Female
Material - Metal	Copper
Material - Plating Mating	Gold
Net Weight	0.225/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.50-2.06mm
Wire Size AWG	18, 20
Wire Size mm ²	N/A

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-33468-001-001
Packaging Specification	313025040-000, PK-30907-759, PK-31300-516, PK-31302-480
Product Specification	PS-33468-001-001
Sales Drawing	SD-33468-001-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

[China RoHS](#)

Green Image

Compliant

Not Contained

Search Parts in this Series

[33467 Series](#)

Use With

MX64 Sealed Single Row Crimp Housing 31403 , MX123 Female Receptacle Housing 34566 , 34576