

SPECIFICATIONS			
PARAMETERS	VALUES	UNIT	
DIRECTIVITY	OMINI	-	
SENSITIVTY	-45 ± 2	dB	
STANDARD OPERATING VOLTAGE	4.5	Vdc	
MAX OPERATING VOLTAGE	10	Vdc	
CURRENT CONSUMPTION (MAX)	0.5	mA	
IMPEDANCE	1	KOhm	
SIGNAL TO NOISE RATIO (MIN.)	60	dB	
TERMINAL	SOLDER PADS	-	
INTERNAL CAPACITOR	N/A	pF	

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.

©2003, Projects Unlimited Inc.

REVISION HISTORY				
LTR	DESCRIPTION	DATE	APPROVED	
-	RELEASED FROM ENGINEERING	1/30/2006		
Α	ADDED TERMINAL POLARITY	1/30/2007	R.W.	
В	ADDED TERMINAL DIAMETER	6/23/2010	B.R.	
С	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	9/16/2010	B.R.	
D	REVISED DIMENSIONS	2/14/2020	M.V.	





NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

UNLESS OTHERWISE SPECIFIED:		Designed by
	SIZE	J.A.F.
DIMENSIONS ARE IN MILLIMETERS,		\sim
TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.	A 3	
AOM-6545	5P-R.idw	4

J.A.F.	1/30/2006	E.P.
	pul.	
	a projects unlimited co	

Checked by

Date

٠.	1/30/2006	B.R.	1/30/20	006	9/16/2010
AOM-6545P-R					
Microphone		Edition -	Sheet 1 / 1		

Date

Drawn Date

Approved by