

## Electronic levels NIVELTRONIC

With 2 level and prismatic measuring surfaces



### Application:

For adjustment of horizontal machine beds and for checking the planarity of machine tables and guide surfaces.

### Execution:

- Cast steel housing
- Battery operation (4x 1.5 V micro type AA)
- Displays in mm/m and angular seconds
- With prismatic base
- Inductive measuring system
- With 2 level and prismatic measuring surfaces

### Delivery:

In wooden box



<b>Art. no.</b>	<b>38450 010</b>
<b>Brand</b>	TESA
<b>Manufacturer Part Number</b>	03 130060
<b>Length</b>	200 mm
<b>Height</b>	200 mm
<b>Measuring range 1, level (+/-)</b>	0.75 mm/m
<b>Measuring range 2, level (+/-)</b>	0.15 mm/m
<b>Scale value</b>	0.01 mm
<b>Spirit level error limit</b>	0.005 mm/m
<b>Repetition accuracy, spirit level</b>	0.001 mm/m
<b>Gross Weight</b>	7.000 kg
<b>Product Group</b>	366

### EAN

7630041112221