

Ergonomic WG series workbench with manual height adjustment

Solid beechwood 2000 mm, 2 drawers with full extension, height-adjustable by crank handle

Execution:

- Continuous height adjustment from approx. 740-1040 mm via hand crank (removable)
- Base made of square steel tube, outer 60 x 60 x 2 mm, inner 55 x 55 x 2 mm, with level compensation on all four feet

Advantage:

- Workbench can be quickly and easily adjusted to the desired working height
- Always working at the right height ensures ideal ergonomic conditions
- When you buy this product, you plant a tree and also receive a tree certificate!

Delivery:

Fully assembled including hand crank



Art. no.	50212 344
Number of drawers	2 PCS
Worktop width	2000 mm
Pullout type	Full extension
Worktop height	50 mm
Colour of front	Optional
Worktop depth	700 mm
Cabinet colour	Optional
Functions	RFID possible
Max. height	1040 mm
Min. height	740 mm
Adjustable in height	Yes
Drawer surface	0.27 m ²
Surface	Powder-coated
With single pull-out safety brake	Yes
Load-carrying capacity	800 kg
Lock type	DOM® locking system
Drawer front height	1 x 150 mm, 1 x 180 mm
Dynamic load-carrying capacity	200 kg
Drawer width (inner dimension)	450 mm
Type	Manual height adjustment
Drawer width (inner dimension) x drawer depth (inner dimension)	450 x 600 mm
Material of worktop	Solid beech
Drawer depth (inner dimension)	600 mm
Load-carrying capacity per drawer	70 kg
Material of base frame	Steel plate
Central locking	Yes
Levelling	Yes
Product Group	Prod. Gr. 5BC

EAN

4053625049011