

## Swarf containers, manual tipping

with floor-level emptying option, mobile

### Application:

An indispensable aid for collecting and separating liquids from solids and for transporting waste, bulk materials, chips and mass produced parts of all types.

### Version:

- Skip with sliding handle
- Stable sheet steel structure with edge reinforcement, base frame made of section steel
- With perforated sheet insert for chip collection, hole diameter 3 mm, division 6 mm and drain valve 1"
- Fork pockets with protection against accidental slipping and tipping
- Easily movable with two wheels and one steering wheel (from content of 600 litres with two steering wheels) made of solid rubber, diameter 250 x 60 mm, one steering wheel with wheel brake

### Advantage:

- With floor-level emptying option
- Portable thanks to the integrated wheels, meaning they can be used anywhere
- Manual tilting of the trough ensures that it can be emptied without leaving any material behind, with locking protection that prevents it tipping over

### Delivery:

Goods supplied without packaging as standard. Packaging on request.



<b>Art. no.</b>	<b>50266 140</b>
<b>Volume</b>	0.25 m <sup>3</sup>
<b>Length</b>	1115 mm
<b>Width</b>	820 mm
<b>Tipper edge height</b>	680 mm
<b>Height</b>	990 mm
<b>Fork pocket clearance</b>	465 mm
<b>Fork pocket size (W x H)</b>	170 x 55 mm
<b>Number of wheels</b>	3 PCS
<b>With drain valve</b>	Yes
<b>With stacker seat tilt function</b>	No
<b>With perforated sheet</b>	Yes
<b>Load-carrying capacity</b>	300 kg
<b>Surface</b>	Lacquered
<b>Colour</b>	Light blue RAL 5012

### EAN-Code

4052462041905