

Cordless hammer drill HR140 DZ

suitable for SDS-Plus, Li-ion, 10.8 V, no battery or charger



Application:

For drilling and hammer drilling

Execution:

- Electronically controllable speed
- with unlatch coupling
- with motor brake
- with connection for DX02 dust extraction
- housing construction designed for low-vibration operation

Delivery:

Handle holder, screw M8x120, side handle 36, depth stop, does not include battery or charger



Art. no.	71029 470
Brand	MAKITA
Manufacturer Part Number	HR140DZ
Model	HR140DZ
Manufacturer Article Number	HR140DZ
Battery voltage	10.8 V/AC
Battery included	No
Number of rechargeable batteries/batteries	0
Max. impact energy	1 J
Max. impact rate	4900 rpm
Max. drilling diameter in wood	13 mm
Max. drilling diameter in steel	10 mm
Min./max. idle speed	0-850 rpm
Min./max. idle impact rate	0-4900 rpm
Weight	2.6 kg
Suitable for tool holding device	SDS-plus
With battery capacity display	No
With speed control	Yes
With quick clamping system	No
With right/left-hand rotation	Yes
With working lights	Yes
Length x width x height	246 x 74 x 198 mm
Max. drilling diameter in concrete	14 mm
Gross Weight	2.120 kg
Product Group	715

EAN

0088381849050