

NYS229

2 pole open 1/4" jack, 2 contacts, with washer and nut, panel thickness 3.5 mm, with 0.205" faston tabs



Technical Information [▼hide](#)

Product

Title	NYS229
-------	--------

Electrical

Dielectric strength	0.5 kVdc
---------------------	----------

Insulation resistance	≥ 1 GΩ
-----------------------	--------

Rated current	depends on mated connector
---------------	----------------------------

Contact resistance	depends on mated connector
--------------------	----------------------------

Mechanical

Insertion force	≤ 20 N
-----------------	--------

Withdrawal force	≥ 10 N
------------------	--------

Lifetime	1000 mating cycles
----------	--------------------

Panel thickness	3.5 mm
-----------------	--------

Material

Insulation	Insulation board
------------	------------------

Environmental

Temperature range	-20 °C to +70 °C
-------------------	------------------