## RS PRO Energy efficient Panel Heater



with integral 7 day 24 hour LCD electronic timer and controls Stock No: 1962386,1962388







The 24/7 Panel Heater connects directly to the permanent electricity supply offering two heat output settings depending on your heating needs. The timer option allows user to select one of 12 pre-set programmes or create a customised 'DIY' heating programme. Wall fixtures are included.

## **Key Features**

- Silent in operation
- Lot 20 compliant
- High efficiency of airflow with over 95% of used energy creating heat
- User friendly LCD display screen
- 12 pre-set programmes available
- 1 user defined programme available
- Program and real-time clock memory function
- Thermostat for temperature setting (5°C-30°C)
- Adjustable temperature in Normal and Economic modes
- 24 hour On/Off Timer
- · Anti-frosting function
- Ionizer function
- · Child safety lock
- · Over-heat safety protection
- IP24 rated

## **Technical Specifications**

Model	494823	494824	494825
Power	1000W	1500W	2000W
Colour	White	White	White
Heating setting	1000W	1500W	2000W
Heating area	10-13m <sup>2</sup>	15-18m²	20-23m <sup>2</sup>
Voltage	230-240V (50Hz)	230-240V (50Hz)	230-240V (50Hz)
Approval	CE, EMC, LVD, RoHS, ERP	CE, EMC, LVD, RoHS, ERP	CE, EMC, LVD, RoHS, ERP
Product size (HxWxD)	440 x 455 x 125mm	440 x 615 x 125mm	440 x 775 x 125mm
Packaged size (HxWxD)	505 x 520 x 155mm	505 x 680 x 155mm	505 x 840 x 155mm
Heater weight	4kg	5.1kg	6.5kg
Gross weight	5.1kg	6.3kg	7.9kg